

# LIBERTY LINER II

VSDT

Gel Liner – Evacuation Valve  
with Distal Attachment

**NEW PIN!**

Can be used with most other shuttle locks!



Items sold separately.  
See reverse page.



## DESCRIPTION

ALPS™ Liberty Liner II allows the expulsion of sweat and air through a built-in valve either through the pin or reducer. The one-way evacuation valve has been strategically placed distally to evacuate any air between the user's skin and the liner.

## TOP FEATURES



Provides superior fit



Built-in valve to expel air



Liner can be used for pin-lock



Available in 6mm uniform thickness



HIGH DENSITY (HD) GEL



LOCKING



KNITTED FABRIC  
Seamless, Differentiated Stretch, Integrated Matrix




#makinglivesbetter

MAKING LIVES BETTER


# CROSS SECTION DIAGRAM

6.0MM UNIFORM



## HOW TO SIZE

Measurements taken 6cm from the distal end



MEASURED  
SIZE (CM)



VSDT - LOCKING  
6MM UNIFORM

20-23 cm

VSDT20-6

24-25 cm

VSDT24-6

26-27 cm

VSDT26-6

28-31 cm

VSDT28-6

32-37 cm

VSDT32-6

38-43 cm

VSDT38-6

SOLD SEPARATELY — USE CODES BELOW WHEN ORDERING

PRODUCT IMAGE	PART NAME	PART #
	LIBERTY LINER II REDUCER WITH BUILT-IN VALVE	LDA-764
	LIBERTY LINER II PIN WITH BUILT-IN VALVE <i>Only compatible with ALPS locks</i>	LDP-764
	LIBERTY LINER II PIN WITH BUILT-IN VALVE <i>Compatible with most shuttle locks</i>	LDPU-864



T: 727.528.8566 | 800.574.5426 | F: 727.528.8862

[www.easyliner.com](http://www.easyliner.com) | [info@easyliner.com](mailto:info@easyliner.com)

2895 42nd Avenue North St. Petersburg, Florida 33714

